

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727080020](#)
Status: **Active**
Overview: Mini-Fit Jr. Power Connectors
Description: Mini-Fit TPA2 Receptacle Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Low-Halogen, 20 Circuits

Documents:

Drawing (PDF)	Packaging Specification 1727080001-PK-000 (PDF)
Product Specification 2029880001-PS-000 (PDF)	Test Summary 2029880001-TS-000 (PDF)
Application Specification AS-172718-0000-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	172708
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information.
Overview	Mini-Fit Jr. Power Connectors
Product Name	Mini-Fit TPA2
UPC	191128361477

Physical

Circuits (maximum)	20
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.538/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-172718-0000-001
Packaging Specification	1727080001-PK-000
Product Specification	2029880001-PS-000
Sales Drawing	SD-172708-0000-000
Test Summary	2029880001-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172708](#) Series

Mates With

Mini-Fit TPA2 Plug Housing [172762](#) ,
[172767](#)
Mini-Fit Jr. Plug Housing [5559](#)

Mini-Fit Jr. Headers [5566](#) , [5569](#)

Use With

Mini-Fit TPA2 Female Terminal [172718](#) ,
[202988](#)
Mini-Fit TPA2 Retainer [172709](#)