

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062835001](#)
Status: **Active**
Overview: [QSFP+ Interconnect Solution](#)
Description: Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125µm 3mm Round Cable Plenum, Standard Bandwidth (OM 2), 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Fiber Optic Assemblies
Series	106283
Boot Type	N/A
Connector to Connector	MTP-to-LC
Mode	Multimode Enhanced
Overview	QSFP+ Interconnect Solution
Product Name	iPass+™ HD, MPO, QSFP+
UPC	822350976718


Physical

Cable Length	1.0m
Cable Size	50/125µm
Fiber (Core/Cladding)	50/125µm
Net Weight	46.400/g
Single Ended	No
Wire/Cable Type	Round

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-106283-5XXX
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant/Exempted

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[106283](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION