

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020088](#)  
**Status:** **Active**  
**Overview:** C-Grid Connector Products  
**Description:** SL Crimp Terminal, Series 70058, Female, 22-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel

**Documents:**

[Drawing \(PDF\)](#) [Product Specification TS-70058-001-001 \(PDF\)](#)  
[Product Specification PS-70058-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-70400-001 \(PDF\)](#)

**General**

Product Family Crimp Terminals  
Series [70058](#)  
Application Signal, Wire-to-Board, Wire-to-Wire  
Crimp Quality Equipment Yes  
Overview [C-Grid Connector Products](#)  
Packaging Alternative [16-02-0104 \(Bag\)](#)  
Product Name CyClone, SL  
UPC 800753596030

**Physical**

Gender Female  
Material - Metal Phosphor Bronze  
Material - Plating Mating Gold  
Material - Plating Termination Tin  
Net Weight 0.073/g  
Packaging Type Reel  
Plating min - Mating 0.762µm  
Plating min - Termination 1.905µm  
Termination Interface: Style Crimp or Compression  
Wire Insulation Diameter 1.63mm max.  
Wire Size AWG 22, 24  
Wire Size mm<sup>2</sup> N/A

**Solder Process Data**


Lead-freeProcess Capability N/A

**Material Info**

Engineering Number 70058-0026

**Reference - Drawing Numbers**

Product Specification PS-70058-001, PS-70400-001, TS-70058-001-001  
Sales Drawing 700580001-SD-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[70058 Series](#)

**Use With**

SL Crimp Housing [70066](#) , [70450](#)  
<br>CyClone Connector [73099](#)