

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191540023**
Status: **Active**
Overview: Splices
Description: InsulKrimp Butt Splice for 14-16 AWG Wire

Documents:

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-007-001 (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series 19154
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Splices
 Product Name Butt, InsulKrimp
 UPC 800753108882

Physical

Barrel Type Closed
 Color - Resin Blue
 Flammability 94V-2
 Insulation PVC
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin PVC
 Net Weight 1.629/g
 Packaging Type Bag
 Wire Size AWG 14, 16

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number BS-V-331X

Reference - Drawing Numbers

Product Specification PS-19902-007-001, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing SD-19154-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19154 Series