

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030084](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19203](#)
 Comments 1200° F (649° C)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [High-Temperature Temp Terms Terminals and Splices](#)
 Product Name Krimptite, Temp-Terms
 Type Ring
 UPC 800753049949

Physical

Barrel Type Closed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 0.628/g
 Packaging Type Adhesive Tape on Reel
 Stud Size 8 (M4)
 Wire Size AWG 14, 16
 Wire Size mm² 1.00-2.50

Material Info

Engineering Number BB-U-137-08T

Reference - Drawing Numbers

Product Specification PS-19902-011-001
 Sales Drawing BBCD10104



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

Green Image

Not Relevant

Missing Compliance
 Data

Not Contained

Search Parts in this Series

[19203 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION