

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192050004](#)
Status: **Active**
Overview: [Splices](#)
Description: VersaKrimp Parallel Splice for 8 AWG Wire

Documents:

| | |
|--|--|
| Drawing (PDF) | Product Specification PS-19902-013-001 (PDF) |
| Product Specification PS-19902-011-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

General

| | |
|-------------------------|-------------------------|
| Product Family | Splices |
| Series | 19205 |
| Crimp Quality Equipment | Yes |
| Mil-Spec | N/A |
| Overview | Splices |
| Product Name | Parallel, VersaKrimp |
| UPC | 800755060843 |

Physical


| | |
|--------------------------------|-----------------|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 1.887/g |
| Packaging Type | Bag |
| Wire Size AWG | 8 |

Material Info

| | |
|--------------------|-------|
| Engineering Number | D-355 |
|--------------------|-------|

Reference - Drawing Numbers

| | |
|-----------------------|------------------------------------|
| Product Specification | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing | SD-19205-007 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19205 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION