

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192150034](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** VersaKrimp Butt Splice for 8 AWG Wire

**Documents:**

|  |  |
|--|--|
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Product Specification PS-19902-013-001 (PDF)</a> |
| <a href="#">Product Specification PS-19902-011-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

**General**

|                         |                         |
|-------------------------|-------------------------|
| Product Family          | Splices                 |
| Series                  | <a href="#">19215</a>   |
| Crimp Quality Equipment | Yes                     |
| Mil-Spec                | N/A                     |
| Overview                | <a href="#">Splices</a> |
| Product Name            | Butt, VersaKrimp        |
| UPC                     | 800755062564            |

**Physical**

|                                |                 |
|--------------------------------|-----------------|
| Barrel Type                    | Closed - Brazed |
| Insulation                     | None            |
| Material - Metal               | Copper          |
| Material - Plating Mating      | Tin             |
| Material - Plating Termination | Tin             |
| Net Weight                     | 4.282/g         |
| Packaging Type                 | Carton          |
| Temperature Range - Operating  | 149°C           |
| Wire Size AWG                  | 8               |

**Electrical**

|                   |      |
|-------------------|------|
| Voltage - Maximum | 600V |
|-------------------|------|

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

**Material Info**

|                    |       |
|--------------------|-------|
| Engineering Number | D-354 |
|--------------------|-------|

**Reference - Drawing Numbers**

|                       |                                    |
|-----------------------|------------------------------------|
| Product Specification | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing         | SD-19215-007                       |



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19215 Series](#)