

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192730008**
Status: **Active**
Overview: Quixon Terminals
Description: Quixon Quick Disconnect, Krimptite Style, Female, Un-insulated, 14-16 AWG, Loose

Documents:

3D Model Product Specification PS-19902-013-001 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)

Agency Certification

CSA LR18689
 UL E79133

General

Product Family Quick Disconnects
 Series 19273
 Comments Low Insertion Force
 Crimp Quality Equipment Yes
 Insulated No
 Overview Quixon Terminals
 Product Name Krimptite, Quixon
 Type Quick Disconnect
 UPC 884982564923

Physical

Barrel Type Closed
 Gender Female
 Glow-Wire Capable No
 Insulation None
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.648/g
 Orientation Straight
 Packaging Type Bag
 Tab Thickness 0.41mm
 Tab Width 7.87mm
 Temperature Range - Operating -55° to +105°C
 Wire Size AWG 14, 16

Electrical


Voltage - Maximum Per Wire Specification

Material Info

Engineering Number BB-1141-LIF

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19273-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19273 Series