

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0197244102](#)
Status: **Active**
Overview: [Snap Plugs and Receptacles](#)
Description: VibraKrimp Snap Plug for 14-18 AWG Wire, Strain Relief, Plated, Fits Diameter 3.96mm

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-19724-001 \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	19724
Comments	Open Barrel
Crimp Quality Equipment	Yes
Insulated	No
Overview	Snap Plugs and Receptacles
Product Name	VibraKrimp
Type	Snap Plug
UPC	800753118836

Physical

Barrel Type	Open
Gender	Male
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.607/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Wire Insulation Diameter	N/A
Wire Size AWG	14, 16, 18


Electrical

Voltage - Maximum	N/A
-------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19724-001
Sales Drawing	SD-19724-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19724 Series](#)