

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0354529902](#)  
**Status:** **Active**  
**Overview:** Standard Quick-Disconnect Terminals  
**Description:** 6.35mm Tab Heavy, Tab Terminal, A-type, 12-14 AWG (3.00-2.00mm<sup>2</sup>), Pre-Tin Plated

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-35452-002-001 (PDF)</a>
<a href="#">Product Specification PS-35546-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Quick Disconnects
Series	<a href="#">35452</a>
Crimp Quality Equipment	Yes
Insulated	No
Overview	<a href="#">Standard Quick-Disconnect Terminals</a>
Product Name	N/A
Type	Quick Disconnect
UPC	756054282151

**Physical**

Barrel Type	Open
Gender	Male
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Net Weight	1.258/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40°C to +120°C
Wire Size AWG	12, 14

**Electrical**

Voltage - Maximum	250V
-------------------	------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-35452-002-001
Product Specification	PS-35546-002
Sales Drawing	SD-35452-001

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[35452](#) Series

**Use With**

[35546](#) , [35547](#)