

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0354539902](#)
Status: **Active**
Overview: Standard Quick-Disconnect Terminals
Description: 6.35mm Tab Heavy, Tab Terminal, Type B, 12-14 AWG (3.00-2.00mm²), Pre-Tin Plated

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-35452-002-001 \(PDF\)](#)
[Product Specification PS-35546-002 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	35453
Crimp Quality Equipment	Yes
Insulated	No
Overview	Standard Quick-Disconnect Terminals
Product Name	N/A
Type	Quick Disconnect
UPC	756054282205

Physical

Barrel Type	Open
Gender	Male
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Net Weight	0.973/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40° to +120°C
Wire Size AWG	12, 14


Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35452-002-001
Product Specification	PS-35546-002
Sales Drawing	SD-35452-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[35453](#) Series

Use With

[35546](#) , [35547](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust Applicator for 6.35mm Tab Heavy Terminals, Type A, 14-16 AWG	0639007800

This document was generated on 09/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION