

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0469990101](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK High Pressure Crimp Terminal 7879, 24-30 AWG, Bag Tin \(Sn\)](#)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)  
[Product Specification PS-7879-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family [Crimp Terminals](#)  
Series [7879](#)  
Application [Signal, Wire-to-Board](#)  
Crimp Quality Equipment [Yes](#)  
Overview [KK® Interconnect System - Molex](#)  
Packaging Alternative [50-29-1900 \(Reel\)](#)  
Product Name [KK High Pressure](#)  
UPC [884982607262](#)

**Physical**

Gender [Female](#)  
Material - Metal [Brass](#)  
Material - Plating Mating [Tin](#)  
Material - Plating Termination [Nickel](#)  
Net Weight [0.118/g](#)  
Packaging Type [Bag](#)  
Plating min - Mating [2.540µm](#)  
Plating min - Termination [2.540µm](#)  
Termination Interface: Style [Crimp or Compression](#)  
Wire Insulation Diameter [1.57mm max.](#)  
Wire Size AWG [22, 24, 26, 28, 30](#)  
Wire Size mm² [N/A](#)

**Solder Process Data**


Lead-freeProcess Capability [N/A](#)

**Material Info**

Engineering Number [7879-1\(P154\)L](#)

**Reference - Drawing Numbers**

Packaging Specification [PK-2759-002-001](#)  
Product Specification [PS-7879-001](#)  
Sales Drawing [SD-7879](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[7879 Series](#)