

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5019123990](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 0.30mm Pitch Easy-On FPC Connector, Right-Angle, Surface Mount, Bottom Contact Style, 1.80mm Mated Height, 39 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-501912-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-501912-001-001 \(PDF\)](#)

General

Product Family FFC/FPC Connectors
 Series [501912](#)
 Overview FFC-FPC (SMT)
 Product Name Easy-On
 UPC 822350342650

Physical

Actuator Type Flip
 Circuits (Loaded) 39
 Circuits (maximum) 39
 Color - Resin Black, Natural
 Contact Position Bottom
 Durability (mating cycles max) 20
 Mated Height 1.80mm
 Material - Metal Copper, Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Material - Resin High Temperature Thermoplastic
 Net Weight 180.684/mg
 Number of Rows 1
 Orientation Right Angle
 PCB Locator No
 PCB Mounting Surface Mount
 PCB Retention None
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 0.30mm
 Pitch - Termination Interface 0.30mm
 Plating min - Mating 0.102µm
 Plating min - Termination 0.051µm
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -40° to +105°C
 Wire/Cable Type FPC only


Electrical

Current - Maximum per Contact 0.2A
 Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-501912-001-001
 Product Specification PS-501912-001-001
 Sales Drawing 5019120000-000, 5019121000-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501912 Series](#)

This document was generated on 09/04/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION