

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0513533000**
Status: **Active**
Overview: MicroClasp Wire-to-Board System
Description: 2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 30 Circuits, White

Documents:

[3D Model](#) [Packaging Specification SPK-51353-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51353-003-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series 51353
Application Signal, Wire-to-Board
Overview MicroClasp Wire-to-Board System
Product Name MicroClasp
UPC 756054235850


Physical

Circuits (maximum) 30
Color - Resin White
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1339.000/mg
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.00mm
Stackable No
Temperature Range - Operating -25° to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-51353-001-001
Product Specification PS-51353-003-001
Sales Drawing SD-51353-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

51353 Series

Mates With

55917 Vertical Header with Kinked PC Tails,
55959 Right Angle Header, 501844 Vertical
Header

Use With

56134 Terminal