

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0675810000**  
**Status:** **Active**  
**Overview:** Serial ATA Connectors and Cable Assemblies  
**Description:** 1.27mm Pitch Serial ATA Crimp Terminal for Power Cable Receptacle, Gold (Au) Flash Plating, with Reel Direction - Type 1, Lead free

**Documents:**

[3D Model](#) [Product Specification PS-67490-002-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	67581
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<a href="#">Serial ATA Connectors and Cable Assemblies</a>
Product Name	Serial ATA
UPC	800756591346

**Physical**

Durability (mating cycles max)	50
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.152/g
Packaging Type	Reel
Plating min - Mating	0.051µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.20-1.60mm
Wire Size AWG	18, 20, 22
Wire Size mm <sup>2</sup>	2.00-3.79

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	15V DC


**Solder Process Data**

Lead-free Process Capability	WAVE
------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Crimp Specification	CS-67581-001
Product Specification	PS-67490-002-001
Sales Drawing	SD-67581-001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[67581](#) Series

**Use With**

[67582](#) Crimp Housing