

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0688014084](#)

Status: **Active**

Overview: Pico-EZmate Harness for Bridgelux Vero and Similar LED COB Arrays

Description: Pico-EZmate-to-Pigtail Cable Assembly, 2 Circuits, 28 AWG fused to 20 AWG Pigtails, Stripped, Cable Length 0.152m

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-68801-002-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	68801
Assembly Configuration	Single Ended Connector
Connector to Connector	Pico-EZmate-to-Pigtail
Overview	<u>Pico-EZmate Harness for Bridgelux Vero and Similar LED COB Arrays</u>
Product Name	Pico-EZmate
UPC	887191282299

Physical

Cable Length	0.152m
Circuits (Loaded)	2
Color - Resin	White
Gender	Male-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Resin	Nylon Alloy
Net Weight	2.000/g
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	UL 1371 VW-1 Fused to UL 1569


Electrical

Current - Maximum per Contact	2.8A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Product Specification	PS-68801-002-001
Sales Drawing	SD-68801-086



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[68801](#) Series

Mates With

Bridgelux Vero Array Holder