

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0845100004**
Status: **Active**
Overview: XRC (Extra Rugged Circular) Sealed Plugs and Receptacles
Description: XRC Sealed Plug with Socket Insert, Shell Size 24, 31 Circuits, without Collar

Documents:

[3D Model](#) [Packaging Specification PK-84501-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84501-001-001 \(PDF\)](#)

Agency Certification

UL E152602

General

Product Family Crimp Housings
Series [84510](#)
Application Power, Wire-to-Wire
Comments IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)

Overview

[XRC \(Extra Rugged Circular\) Sealed Plugs and Receptacles](#)

Product Name XRC
UPC 883906514945

Physical

Circuits (maximum) 31
Circuits Detail 31
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Net Weight 59.420/g
Number of Rows 0
Packaging Type Tray
Panel Mount Yes
Pitch - Mating Interface N/A
Pitch - Termination Interface N/A
Temperature Range - Operating -40° to +130°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-84501-001-001
Product Specification PS-84501-001-001
Sales Drawing SD-84510-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[84510](#) Series

Mates With

[84511](#) Receptacle

Use With

[84525](#) XRC Sealed Terminal Socket