

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008560115](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 254 Crimp Terminal 4809, 22-30 AWG, Selective Gold (Au), Bag

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-99020-0088-001 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [4809](#)
 Application Signal, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-56-0120 \(Reel\)](#)
 Product Name KK 254
 UPC 800753745940

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Net Weight 0.066/g
 Packaging Type Bag
 Plating min - Mating 0.432µm
 Plating min - Termination 0.051µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 4809-(550)L

Reference - Drawing Numbers

Product Specification PS-10-07-001, PS-99020-0088-001
 Sales Drawing SD-4809-*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[4809 Series](#)

Use With

[6471 2.54mm Pitch KK Crimp Terminal Housing](#)