

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0887689810**  
**Status:** **Active**  
**Overview:** High Definition Multimedia Interface (HDMI)\* Products  
**Description:** HDMI\*-to-HDMI\* Cable Assembly, 28 AWG, 2.0m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-88768-002-001 \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	88768
Assembly Configuration	Dual Ended Connectors
Connector to Connector	HDMI-to-HDMI
Overview	High Definition Multimedia Interface (HDMI)* Products
Product Name	HDMI
UPC	756054858448

**Physical**

Cable Length	2.0m
Circuits (Loaded)	19
Color - Resin	Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Low Density Polyethylene
Net Weight	143.150/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.813µm
Plating min - Termination	1.270µm
Single Ended	No
Termination Interface: Style	Through Hole
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round


**Electrical**

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shielded	Yes
Voltage - Maximum	40V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-88768-002-001
Sales Drawing	SD-88768-9810, SD-887689810



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

88768 Series