

Full screen 5.7" flagship smartphone featuring fingerprint scanner, 4G support, advanced cameras and slim metal body



Touch Id



1440x720
IPS 2.5D Display



Full screen



RAM



13.0Mpx AF
with Flash



3000mAh battery
Fast charge



- Full screen experience: see more and hold less with 5.7" IPS display with 18:9 aspect ratio. Enjoy the comfort of bezel-less phone with HD+ resolution
- Fingerprint scanner: protects your data in a more reliable and intelligent way
- Beautiful design: slim metal body together with 2.5D curved screen glass ensure gorgeous look. Smartphone is available in trendy color options: golden, blue and black
- Speed in your palm: 4G LTE Internet connection gives you ability to do more: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before

- Photo and video: advanced 13.0MP AF camera with LED-flash ensures excellent clear & vivid shots
- Selfie expert: 5.0MP camera with flash light and a range of features for high quality photos
- High performance multitasking and energy saving: based on 64-bit quad core processor and 2GB RAM
- Capacious: 16GB of internal storage on board and possibility to expand it with microSD cards up to 32GB
- Dual SIM: for optimizing budget on calls and Internet

SIM card slot	Dual SIM: LTE + WCDMA
Display	Size: 5.7" Resolution: HD+ (1440 x 720), 18:9 Technology: IPS, 2.5D curved glass
Processor	MT6737 1.3 GHz 64-bit quad core
Memory	Built-in: 2 GB RAM + 16 GB eMMC Expandable: slot for microSD™ card up to 32GB
Power	3000 mAh Li-ion battery with fast charge technology
OS	Android 7.0 Nougat
Imaging	Front: 5.0MP with flash light Rear: 13.0MP AF with flash light

Network	4G LTE: 800/1800/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900MHz
Connectivity	BT 4.0+HS, Wi-Fi: 802.11b g n USB: microUSB 2.0, OTG
Audio	Mic, speakers, 3.5 jack
Built-in devices	Fingerprint scanner, GPS, FM
Dimensions	153 x 73 x 8.2 mm
Weight	167g (with battery)
In the box	USB cable, AC charger, screen protective film