


Product Summary

The Gazelle Pro is an omni-directional TV and radio aerial designed for mobile and touring vehicles. The enhanced design maintains the established performance and sleek aerodynamics of the original Gazelle, with the addition of a new mounting foot for improved installation.




Enhanced installation




Grey variant

Unique and Innovative Features




Omni-directional

By receiving signals through 360 degrees, the Gazelle Pro requires no manual directional alignment for effortless use. Simply re-scan and watch TV.



Sleek Aerodynamic Design

The low profile and streamline design not only makes the Gazelle look great, but also offers aerodynamic benefits when travelling.



Compact Roof Mounting


The compact size occupies minimal roof space, allowing it to be mounted in almost any position.

Unique and Innovative Features - Continued




Variable Signal Booster

2 outputs and adjustable gain control from 0-18dB allows the user to maximise signal in both high and low signal strength areas.



Telescopic VHF Aerial Option

The telescopic VHF aerial can be attached to provide FM and DAB radio channels as well as some TV channels across Europe.



Flexible Installation

The unique mounting foot can be fixed using a wet Silicone seal or the provided EPDM seal. Both methods require a single hole for the coaxial cable to pass through.



Easy Aerial Head Unit Installation

An integrated push fit connector allows the aerial head unit to be connected and disconnected quickly and conveniently.



Optional Foot Clamp

Overcomes the need for fixings into the roof when used with a wet seal and offers a tidy cable entry point inside the vehicle.

Features

- Receives all available digital terrestrial TV and radio signals
- Designed and tested for outdoor use
- High quality, durable and robust construction
- Designed and manufactured in the UK
- 2 year guarantee

Specifications

Application:	Any mobile touring vehicles including motorhomes, caravans, RV's, HGV's and marine	Power:	Requires 12/24V or 230V (subject to variant) to power Variable Signal Booster
Compatibility:	SD, HD, 3D and 4K TV FM and DAB radio	Mounting:	Can be mounted using flexible adhesive sealant or using screws and the EPDM seal included
Frequency Range:	Wideband for UHF/VHF TV and radio (40 - 860 MHz)	Housing:	UV Stable Injection Moulded ABS
Gain:	Up to 18dB with Variable Signal Booster (included)	Aerial Height:	14cm
		Aerial Weight:	0.9kg


Product Contents

- Aerial Head Unit
- Mounting Foot with Integrated 5 Metre Coaxial Cable
- Clamping Tool
- Telescopic VHF Aerial
- 1m F to Coaxial Flylead
- Variable Signal Booster and Fused Power Lead
- Transformer (230V Variant Only)
- EPDM Water Ingress Seals
- Roof Mounting Kit and Fixings
- Instructions

Product Codes & Variants

B2414	12/24V Gazelle Pro - Omni-directional Mobile TV and Radio Aerial - White
B2415	12/24V/230V Gazelle Pro - Omni-directional Mobile TV and Radio Aerial - White
B2414/G	12/24V Gazelle Pro - Omni-directional Mobile TV and Radio Aerial - Grey

Product Dimensions



Packaging Details

Retail Packaging Style:	Art carton
Packaging Dimensions:	(H x W x D): 314mm x 314mm x 118mm
Packaged Gross weight:	1415g
Barcode Numbers:	B2414: 5016163 513429
	B2415: 5016163 513412
	B2414/G: 5016163 522513

Product Approvals and Packaging Symbols



Card