

LC-60UI7652K

# 60" 4K ULTRA HD

The LC-60UI7652K is a 4K Ultra High Definition Smart LED TV with exceptional picture quality.



NETFLIX

HDR  
HIGH DYNAMIC RANGE

400

ACE PRO ULTRA  
Picture Processing Engine

HDMI

FreeviewHD

SAORVIEW

DVB S2

## Highlights

SCREEN SIZE 152 cm (60")

HARMAN/KARDON SPEAKER SYSTEM

HD TUNER DVB-T/T2/C/S/S2 (MPEG4 + HEVC/H.265)

WIRELESS CONNECTION WITH MOBILE DEVICES

SD CARD READER

HIGH DYNAMIC RANGE

3x HDMI 2.0 INPUTS

4K UHD SMART TV

SOUND SYSTEM BY

harman/kardon®

Smart Ultra HD UI7652 series provides a wide range of connection possibilities. Three USB ports and three HDMI 2.0 ports are able to receive 2160p@60Hz signal.

HDR technology can deliver better contrast and increased brightness compared with standard TV sets.

PVR is not available in DACH-region and Italy

Sharp.eu/av | #SharpBeOriginal

**SHARP**  
Be Original.

## DISPLAY

Diagonal screen size cm / inch	152/60
Panel resolution	3840x2160
HDR support	YES
Active motion	400
Backlight	D-LED
Dynamic contrast	1 000 000:1
Panel bit depth	10bits (8bits + FRC)

## AUDIO SYSTEM

Speaker	2.1 System
	Full-range + silk tweeter + woofer
Speaker Power	2x10W (8 ohm) + 20W subwoofer (8 ohm)
Sound Technology	Harman-Kardon
Sound System	B/G, D/K, I, L, NICAM/A2
Sound Settings	Sound Equalizer
Audio decoder	Dolby Digital/Digital+
Audio enhancement solution	DTS Studio Sound™

## TUNER

TV system	ATV	PAL, SECAM
	DTV	DVB-T/T2/C/S/S2 (MPEG4 + H.265/HEVC)

## FUNCTION

SHARP AQUOS NET+ Apps store	YES
Pre-install Apps	YouTube, Deezer, Netflix and many more
BBC iPlayer	YES
Miracast	YES
WiFi	YES
Video system	HEVC/H.265, MPEG4/H.264, VP9
USB Video	AVI/MKV/WebM/WMV/ASF/MP4/MOV/MKV/DAT/VOB/TS/MPG/MPEG/FLV/SWF/3GPP/3GP
USB Music	MP3/AVI/ASF/DIVX/WAV/MKV/3GPP/3GP/M4a/MP4/MOV/AC3/LPCM/OGG
USB Photo	JPG, JPEG, BMP, PNG
PVR Ready with timeshift	YES (FAT32 only)
USB Software Update	YES
USB file system	FAT16/FAT32/NTFS
HDMI-CEC	YES
HDMI-ARC	YES (HDMI3)
OAD	YES
Digital Programme List	YES
Hotel Mode	NO

## CONNECTORS

HDMI-in 2.0	YES (3x)
USB	YES (3x)
SD Card slot	YES
Common interface / CI+	YES
Antenna In (RF)	YES
Sat In	YES
Component/YPbPr	YES
AV Composite input + Audio In	YES
Audio out / Headphone Jack	YES
Digital Optical Audio Output	YES
RJ 45 (LAN)	YES

## OTHERS

Power Requirements	AC 220-240V ~ 50Hz
Safety Logo Certification	CE (EMC), CB (Safety), ErP (Energy) etc
ErP Compliant	A/A+
Power Consumption (ecomode/standard/max)	TBD
Power Consumption (Standby Mode)	<0.50 W
VESA standard (mm)	200 x 200
EAN	4974019969039
Net size with stand (W x H x D in mm):	1357,5 x 839,7 x 280,0
Net size without stand (W x H x D in mm):	1357,5 x 783,5 x 76,5
Dimension between stand feet (in mm):	1114,0
Box size (W x H x D in mm):	TBD
Net weight (kg)	18,3
Gross weight (kg)	TBD

## PRODUCT FICHE

Supplier trademark Sharp	LC-60UI7652K
Energy class	A / A+
Screen size	152 cm / 60 inches
Power consumption	TBD W

Annual energy consumption*	TBD kWh
Standby power consumption	<0.50 W
Off mode power consumption	Not applicable
Screen resolution	3840 (H) × 2160 (V)

\* - Energy consumption XYZ kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how television is used.

For DTS patents, see <http://patents.dts.com>. Manufactured under license from DTS Licensing Limited. DTS, the Symbol, & DTS and the Symbol together are registered trademarks. DTS Studio Sound is a trademark of DTS, Inc. © DTS, Inc. All Rights Reserved.