



VT-7652 SLEEK GU10 WALL FITTING(ALUMINIUM) ROUND-BLACK 2 WAY IP44

Dimensions  
**92x68x80mm**

SKU:7509

**2 YEARS**  
WARRANTY



## Technical Information

Holder Type:	GU10	Dimmable:	No
Shape:	Round	Warranty (Years):	2
Unit Color:	Black	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-25 to +50°C
Energy Rating:	Fitting	Input Power:	AC:220-240V,50Hz
IP Rating:	IP44		



## Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.575
Unit CBM	0.001344

### Listing Details

EAN Code	3800157617680
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
Qty Per Pallet	672

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES