



VT-8051 PIR CEILING SENSOR-WHITE

Dimensions
10x78x82mm

SKU:1356

2 YEARS
WARRANTY



Technical Information

Ambient Light:

Detection Distance: **Max. 6m**

Detection Motion Speed: **0.6-1.5m/s**

Rated Load: **Max. 1200W**

Time Delay: **Min. 10sec±3sec, Max. 15min±2min**

Detection Range: **360°**

Unit Color: **White**

Body Type: **PC**

Sensor Type: **Infrared**

Long life: **20,000 Hours**


IP Rating: **IP20**

Dimmable: **No**

Warranty (Years): **2**

Operation Temperature: **-25 to +50°C**

Input Power: **AC:220-240V,50/60Hz**



Features

- ✓ Infrared Motion Sensor adopts good sensitivity detector and integrated circuit
- ✓ Adjustable Time Delay - Ambient light - Detection distance for versatile scenarios
- ✓ Manual override functionality - IR Sensor can be set in Automatic mode or the sensor can be switched on
- ✓ Detection range of 180°(Wall Mounted) and 360° (Surface, Recessed Mounted)
- ✓ High quality receptors for instant functioning
- ✓ Effective system for energy saving and safety
- ✓ Compatible with V-TAC models

Packaging

Unit Details

Net Weight	0.094
Gross Weight(GW) Kgs	0.133
Length(Box)mm	80
Width(Box)mm	100
Height(Box)mm	75
Unit CBM	0.0006

Listing Details

EAN Code 3800157624817



Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	1400

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES