

4G smartphone with 5.5" fullscreen, improved cameras and 4000mAh battery based on Android 8.1 Oreo



HD+ 1440x720
IPS 2.5D curved



4000 mAh
battery



LTE



2GB
RAM
16GB
eMMC



5.0MP
13.0MP AF

- Full screen experience: see more and hold less with 5.5" IPS display with 18:9 aspect ratio. Enjoy the comfort of bezel-less phone with HD+ resolution
- Huge battery: 4000 mAh powerful battery for maximum endurance
- Updated Android OS version: 8.1 Oreo version with improved battery management, security, multitasking and lots of other up-to-date features
- Photo and video: advanced 13.0MP AF camera with flash light ensures excellent clear & vivid shots

- Selfie expert: 5.0MP camera with flash light and a range of features for high quality photos
- High performance multitasking and energy saving: based on quad core processor and 2GB RAM
- Capacious: 16GB of internal storage on board and possibility to expand it with microSD cards up to 128GB
- Speed in your palm: 4G LTE Internet connection gives you ability to do more: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before
- Dual SIM: for optimizing budget on calls and Internet

SIM card slot	Dual SIM: LTE + WCDMA (nano SIM)
Display	Size: 5.5" Resolution: HD+ (1440x720), 18:9 Technology: IPS, full lam, 2.5D curved screen glass
Processor	MT6739 1.3 GHz quad core
Memory	Built-in: 2GB RAM + 16GB eMMC Expandable: slot for microSD™ card up to 128GB
Power	4000 mAh Li-po battery
OS	Android 8.1 Oreo
Imaging	Front: 5.0MP with flash Rear: 13.0MP AF with flash

Network	4G LTE: 800/1800/2100/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900 MHz
Connectivity	Bluetooth 4.0+HS, Wi-Fi: 802.11b/g/n USB: microUSB 2.0
Audio	Mic, speakers, 3.5 jack
Built-in devices	GPS, FM
Dimensions	149 x 71 x 9.9 mm
Weight	175g (with battery)
In the box	USB cable, AC charger, screen protective film