

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347970202](#)
Status: **Active**
Overview: [MX150™ Unsealed Connector System](#)
Description: MX150 Cable Unsealed Male Connector with GM Style Clip, Single Row, 2 Circuits, Polarization B, Natural

Documents:

[3D Model](#) [Packaging Specification PK-31301-695-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	34797
Application	Power, Wire-to-Wire
Comments	GM Clip Slot
Overview	MX150™ Unsealed Connector System
Polarization	B
Product Name	MX150 Unsealed
UPC	884982970762

Physical

Circuits (maximum)	2
Color - Resin	Natural
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	3.310/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	22.0A
-------------------------------	-------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-31301-695-001
Sales Drawing	SD-34797-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[34797 Series](#)

Mates With

[34796](#) 3.50mm Pitch MX150 Cable
Unsealed Female

Use With

MX150 Male Terminal [33000-0001](#) ,
[33000-0002](#) , [33000-0003](#) , [33000-1001](#) ,
[33000-1002](#) , [33000-1003](#)