

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0732511852](#)
Status: **Active**
Overview: Precision Compression-Mount Microwave Test Connectors
Description: 50 Ohms, Precision Test Connector, Optimized SMA Jack, Two Hole Flange, Pressure Contact for Test Boards, One Piece Per Bag

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	RF/Coax Connectors
Series	73251
Comments	EMI/RFI grounding ring
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Type	Subminiature
UPC	883906384029
Wire/Cable Type	N/A

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	1.780/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	Flange
Reverse Polar	No

Electrical

Frequency	27 GHz
Impedance	50Ω

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73251-185-000
---------------	------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

PropRisk

PropRisk

PropRisk

PropSub

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Missing Compliance Data

Cancer

Developmental toxicity

Reproductive toxicity

Lead and its compounds

Not Contained

Search Parts in this Series

[73251](#) Series