

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0732980020](#)  
**Status:** **Active**  
**Overview:** BMA Blind-Mate RF Connectors  
**Description:** 50 Ohms, BMA Jack, 2H Floating Flange Mount for RG-55 Cable

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	RF/Coax Connectors
Series	<a href="#">73298</a>
Comments	Floating
Overview	<u>BMA Blind-Mate RF Connectors</u>
Product Name	BMA
Style	Cable
Type	Subminiature
UPC	883906305277
Wire/Cable Type	RG-55

**Physical**

Cable Attachment	Crimp, Solder
Gender	Jack
Keying to Mating Part	None
Net Weight	7.380/g
Orientation	Straight
PCB Mounting	N/A
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Flange
Reverse Polar	No

**Electrical**

Frequency	22 GHz
Impedance	50Ω

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-73298-002
---------------	--------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - ED/61/2018 (27 June 2018)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

PropRisk

PropRisk

PropRisk

PropSub

RoHS Phthalates

50 Image

Not Relevant

Duty-To-Declare

Cancer

Developmental toxicity

Reproductive toxicity

Lead and its

compounds

Not Contained

**Search Parts in this Series**

[73298](#) Series