

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0733660060](#)  
**Status:** **Active**  
**Overview:** [MCX RF Connectors](#)  
**Description:** 50 Ohms, MCX Jack Receptacle, Vertical, Straight, 7.10mm Height, 1.57mm Standoff Height, Nickel (Ni) Plated Body, Tray

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

|                 |                                   |
|-----------------|-----------------------------------|
| Product Family  | RF/Coax Connectors                |
| Series          | <a href="#">73366</a>             |
| Overview        | <a href="#">MCX RF Connectors</a> |
| Product Name    | MCX                               |
| Style           | PCB                               |
| Type            | Microminiature                    |
| UPC             | 800756205632                      |
| Wire/Cable Type | N/A                               |

**Physical**

|                             |              |
|-----------------------------|--------------|
| Gender                      | Jack         |
| Keying to Mating Part       | None         |
| Net Weight                  | 0.559/g      |
| Orientation                 | Straight     |
| PCB Mounting                | Through Hole |
| PCB Thickness - Recommended | 1.20mm       |
| Packaging Type              | Tray         |
| Panel Mount                 | No           |
| Panel Mount Method          | N/A          |
| Reverse Polar               | No           |

**Electrical**

|           |       |
|-----------|-------|
| Frequency | 6 GHz |
| Impedance | 50Ω   |


**Solder Process Data**

|  |          |
|--|----------|
| Duration at Max. Process Temperature (seconds) | 010      |
| Lead-freeProcess Capability                    | SMC&WAVE |
| Max. Cycles at Max. Process Temperature        | 002      |
| Process Temperature max. C                     | 260      |

**Material Info**

**Reference - Drawing Numbers**

|               |                                |
|---------------|--------------------------------|
| Sales Drawing | SD-73366-006, SD-73366-619-000 |
|---------------|--------------------------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per -ED/01/2018 (15 January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[73366 Series](#)