

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0733870020](#)  
**Status:** **Active**  
**Overview:** Precision Compression-Mount Microwave Test Connectors  
**Description:** 50 Ohms, Precision Test Connector, 2.4mm Jack Receptacle, 2 Hole Flange Mount, with 2 Screws 4.76mm, PCB Thickness 0.56-2.54mm

**Documents:**

[Drawing \(PDF\)](#)      [Application Specification AS-89675-446-001 \(PDF\)](#)  
[Product Specification PS-89675-0410-001 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	RF/Coax Connectors
Series	73387
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	2.40mm
Style	PCB
Type	Subminiature
UPC	884982623309
Wire/Cable Type	N/A

**Physical**

Gender	Jack
Keying to Mating Part	None
Net Weight	2.285/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	Compression
Reverse Polar	No

**Electrical**

Frequency	65 GHz
Impedance	50Ω


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-89675-446-001
Product Specification	PS-89675-0410-001
Sales Drawing	SD-73387-002



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per -ED/01/2018 (15 January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
Prop65	Duty-To-Declare
PropRisk	Cancer
PropRisk	Developmental toxicity
PropRisk	Reproductive toxicity
PropSub	Lead and its compounds
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[73387](#) Series