

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0738380005**  
**Status:** **Active**  
**Overview:** SL Modular Connectors  
**Description:** 2.54mm SL Crimp Housing, Single Row, Version N, TPA with Positive Latch, 5 Circuits, Natural

**Documents:**

[3D Model](#) [Packaging Specification PK-70873-0540 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-73838-005-001 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<u>73838</u>
Application	Signal, Wire-to-Board, Wire-to-Wire
Comments	Terminal Position Assurance (TPA) Piece
Overview	<u>SL Modular Connectors</u>
Product Name	SL
UPC	800754789486

**Physical**

Circuits (maximum)	5
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester Alloy
Net Weight	0.113/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40° to +105°C


**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-70873-0540
Product Specification	PS-73838-005-001
Sales Drawing	SD-73838-004



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

73838 Series

**Mates With**

70018 , 70543 , 70545 , 70553 , 70555 ,  
70107 Version A, 70107 Version B

**Use With**

70058 , 71851 , 73838