

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0988981039**
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: 5.00mm Pitch UCC2 Receptacle Terminal, 0.93mm²; to 2.50mm²;(AWG 14-18), Reel, Pre Tin Plated

Documents:

3D Model	Application Specification AS-98906-001-001 (PDF)
Drawing (PDF)	Packaging Specification 313025040-000 (PDF)
Product Specification PS-98821-001-001 (PDF)	Packaging Specification PK-98898-002 (PDF)
Application Specification AS-98821-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-98898-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	98898
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348815685

Physical

Gender	Female
Material - Metal	High Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.794/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.93-2.50mm
Wire Size AWG	14, 16, 18
Wire Size mm ²	0.93-2.50

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2120519CA201H
--------------------	---------------

Reference - Drawing Numbers

Application Specification	AS-98821-001-001, AS-98898-001-001, AS-98906-001-001
Packaging Specification	313025040-000, PK-98898-002
Product Specification	PS-98821-001-001
Sales Drawing	SD-98898-100



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[98898 Series](#)

Use With

NSCC Receptacle Connector [98819](#) , [98821](#) , [98273](#)