



Orthomat® Lite

Ideal for light to medium use

- Cost-effective anti-fatigue matting.
- Offers the user relief from fatigue caused by standing.
- Insulates against cold concrete floors.
- Ideal for light to medium use in dry environments.
- Pebble surface provides additional traction.

Technical Specification

Material:	Virgin Closed Cell PVC (Foam)
Surface Finish:	Pebble
Product Height:	6mm
Roll Length:	36.5m
Operating Temperature:	0°C to +60°C
Environmental Resistance:	Suitable for dry indoor environments
Typical Applications:	Production lines, assembly areas, packing stations, workbenches
Installation Method:	Loose lay
Cleaning Method:	Brush/Mop the top surface
Product Performance:	Conforms to Slip Resistance Test EN 13552 (Category R10)
Flame Retardancy:	Fire Tested to DIN 54332 (B2) part of DIN 4102
Country of Origin:	China

Sizes	Black	Weight
0.9m x 36.5m x 6mm	CV010001	57.00 kg
0.9m x 6mm x per linear metre	CV010001C	4.30 kg
0.9m x 1.5m x 6mm	CV010002	2.33 kg
0.9m x 2m x 6mm	CV010003	6.92 kg
0.9m x 3m x 6mm	CV010004	4.67 kg
0.9m x 1.82m x 6mm	CV010005	2.83 kg
0.9m x 0.76m x 6mm	CV010006	1.18 kg

