

## IP68 WATERPROOF AND DUSTPROOF PHONE WITH LONG BATTERY LIFE



### Waterproof

- Waterproof and dustproof: protected slim body perfect for extreme conditions
- Long battery life: 1400 mAh li-po battery
- Wide screen: 2.4 inches, comfortable for viewing content
- Dual SIM: for optimizing budget on calls and Internet

- Capture on-the-go: built-in 0.3MP camera with LED-flash
- Light your way: bright torch
- Music on-the-go: earphones in the box, FM and MP3
- Capacious: supports microSD cards up to 32GB
- Connectivity: Bluetooth

#### Hybrid SIM card slot

2 slots: GSM SIM-card + GSM SIM-card/microSD card

#### Display

Size: 2.4"  
Resolution: QVGA (240 x 320)  
Technology: TN

#### Processor

MT6261D

#### Memory

Built-in: 32Mb RAM + 32Mb internal storage  
Expandable: hybrid slot for microSD™ card up to 32GB

#### Power

1400 mAh li-po battery

#### Imaging

Rear: 0.3MP camera with flash light

#### Network

2G GSM: 900/1800 MHz

#### Connectivity

Bluetooth

USB: microUSB 2.0

#### Audio

Mic, speakers, 3.5 jack

#### Built-in

Torch, FM, MP3, MP4, vibrating alerts

#### Dimensions

128 x 59 x 13 mm

#### Weight

133g (with battery)

#### In the box

AC charger, earphones