

TE08205

- **Processor**
 - **CPU Speed**1.4GHz
 - **CPU Type**Quad-Core
- **Display**
 - **Size (Main Display)**5.0" (126.7mm)
 - **Resolution (Main Display)**720 x 1280 (HD)
 - **Technology (Main Display)**PLS TFT LCD
 - **Color Depth (Main Display)**16M
 - **S Pen Support**No
- **Camera**
 - **Rear Camera - Resolution**13.0 MP
 - **Rear Camera - F Number**F1.9
 - **Rear Camera - Auto Focus**Yes
 - **Front Camera - Resolution**5.0 MP
 - **Front Camera - F Number**F2.2
 - **Rear Camera - Flash**Yes
 - **Video Recording Resolution**FHD (1920 x 1080)@30fps
- **Memory**
 - **RAM_Size (GB)**2
 - **ROM Size (GB)**16 GB
 - **Available Memory (GB)***10.5 GB
 - **External Memory Support**MicroSD (Up to 256GB)
- **Network/Bearer**
 - **Number of SIM**Single-SIM
 - **SIM size**Nano-SIM (4FF)
 - **SIM Slot Type**SIM 1 + MicroSD
 - **Infra**2G GSM, 3G WCDMA, 4G LTE FDD, 4G LTE TDD
 - **2G GSM**GSM850, GSM900, DCS1800, PCS1900
 - **3G UMTS**B1(2100), B2(1900), B4(AWS), B5(850), B8(900)
 - **4G FDD LTE**B1(2100), B2(1900), B3(1800), B4(AWS), B5(850), B7(2600), B8(900), B17(700), B20(800)
 - **4G TDD LTE**B38(2600), B40(2300)
- **Connectivity**
 - **ANT+**No
 - **USB Interface**Micro USB
 - **USB Version**USB 2.0
 - **Location Technology**GPS, Glonass, Beidou
 - **Earjack**3.5mm Stereo
 - **MHL**No
 - **Wi-Fi**802.11 b/g/n 2.4GHz
 - **Wi-Fi Direct**Yes
 - **Bluetooth Version**Bluetooth v4.2
 - **NFC**Yes

- **Bluetooth Profiles**A2DP, AVRCP, DI, HFP, HID, HOGP, HSP, MAP, OPP, PAN, PBAP, SAP
- **PC Sync.**Smart Switch (PC version)
- **OS**Android
- **General Information**
- **Color**BLACK
- **Form Factor**Touchscreen Bar
- **Sensors**Accelerometer, Proximity Sensor
- **Physical specification**
- **Dimension (HxWxD, mm)**143.2 x 70.3 x 8.2
- **Weight (g)**142
- **Battery**
- **Internet Usage Time(3G) (Hours)**Up to 12
- **Internet Usage Time(LTE) (Hours)**Up to 14
- **Internet Usage Time(Wi-Fi) (Hours)**Up to 14
- **Video Playback Time (Hours)**Up to 14
- **Standard Battery Capacity (mAh)**2400
- **Removable**No
- **Audio Playback Time (Hours)**Up to 61
- **Talk Time (3G WCDMA) (Hours)**Up to 15
- **Audio and Video**
- **Video Playing Format**MP4, M4V, 3GP, 3G2, WMV, ASF, AVI, FLV, MKV, WEBM
- **Video Playing Resolution**FHD (1920 x 1080) @30fps
- **Audio Playing Format**MP3, M4A, 3GA, AAC, OGG, OGA, WAV, WMA, AMR, AWB, FLAC, MID, MIDI, XMF, MXMF, IMY, RTTTL, RTX, OTA
- **Services and Applications**
- **Gear Support**Gear Circle (Manager Support), Gear Fit, Gear Fit2, Gear1, Gear2, Gear2 Neo, Gear S, Gear S2, Gear S3, Gear IconX
- **S-Voice**No
- **Mobile TV**No