

## TE08206

- 
- 
- **Processor**
  - **CPU Speed**1.6GHz
  - **CPU Type**Octa-Core
- **Display**
  - **Size (Main\_Display)**142.5mm (5.6")
  - **Resolution (Main Display)**1480 x 720 (HD+)
  - **Technology (Main Display)**Super AMOLED
  - **Color Depth (Main Display)**16M
  - **S Pen Support**No
- **Camera**
  - **Rear Camera - Resolution**13.0 MP
  - **Rear Camera - F Number**F1.9
  - **Rear Camera - Auto Focus**Yes
  - **Rear Camera - OIS**No
  - **Front Camera - Resolution**8.0 MP
  - **Front Camera - F Number**F1.9
  - **Front Camera - Auto Focus**No
  - **Front Camera - OIS**No
  - **Rear Camera - Flash**Yes
  - **Front Camera - Flash**Yes
  - **Video Recording Resolution**FHD (1920 x 1080)@30fps
- **Memory**
  - **RAM\_Size (GB)**3
  - **ROM Size (GB)**32
  - **Available Memory (GB)\***22.6
  - **External Memory Support**MicroSD (Up to 256GB)
- **Network/Bearer**
  - **Number of SIM**Single-SIM
  - **SIM size**Nano-SIM (4FF)
  - **SIM Slot Type**SIM 1 + MicroSD
  - **Infra**2G GSM, 3G WCDMA, 4G LTE FDD, 4G LTE TDD
  - **2G GSM**GSM850, GSM900, DCS1800, PCS1900
  - **3G UMTS**B1(2100), B2(1900), B4(AWS), B5(850), B8(900)
  - **4G FDD LTE**B1(2100), B2(1900), B3(1800), B4(AWS), B5(850), B7(2600), B8(900), B12(700), B17(700), B20(800), B66(AWS-3)
  - **4G TDD LTE**B38(2600), B40(2300)
- **Connectivity**
  - **ANT+**No
  - **USB Interface**Micro USB

- **USB Version**USB 2.0
- **Location Technology**GPS, Glonass, Beidou
- **Earjack**3.5mm Stereo
- **MHL**No
- **Wi-Fi**802.11 b/g/n 2.4GHz
- **Wi-Fi Direct**Yes
- **Bluetooth Version**Bluetooth v4.2
- **NFC**Yes
- **PC Sync**.Smart Switch (PC version)
- **OS**Android
- **General Information**
- **Form Factor**Touchscreen Bar
- **Sensors**Accelerometer, Fingerprint Sensor, Hall Sensor, Proximity Sensor
- **Physical specification**
- **Dimension (HxWxD, mm)**149.3 x 70.2 x 8.2
- **Weight (g)**154
- **Battery**
- **Internet Usage Time(3G) (Hours)**Up to 11
- **Internet Usage Time(LTE) (Hours)**Up to 12
- **Internet Usage Time(Wi-Fi) (Hours)**Up to 13
- **Video Playback Time (Hours)**Up to 17
- **Standard Battery Capacity (mAh)**3000
- **Removable**No
- **Audio Playback Time (Hours)**Up to 76
- **Talk Time (3G WCDMA) (Hours)**Up to 21
- **Audio and Video**
- **Video Playing Format**MP4, M4V, 3GP, 3G2, WMV, ASF, AVI, FLV, MKV, WEBM
- **Video Playing Resolution**FHD (1920 x 1080)@60fps
- **Audio Playing Format**MP3, M4A, 3GA, AAC, OGG, OGA, WAV, WMA, AMR, AWB, FLAC, MID, MIDI, XMF, MXMF, IMY, RTTTL, RTX, OTA
- **Services and Applications**
- **Gear Support**Gear Circle (Manager Support), Gear Fit, Gear Fit2, Gear Fit2 Pro, Gear Sport, Gear1, Gear2, Gear2 Neo, Gear S, Gear S2, Gear S3, Gear IconX
- **S-Voice**No
- **Mobile TV**