



Ampliversal 

TERMINALS • TOOLING • CABLE ACCESSORIES

tyco

Electronics

Heatshrink Sleeving

Neoprene Sleeving

Earth Sleeving

Spirap™ Spiral Band

Grommet Strip

Braided Sleeving

tyco
Electronics

Heatshrink Sleeving

Heatshrink Sleeving Dispenser Packs

Thin Wall Polyolefin

2:1 Shrink Ratio - 2.4mm to 38.1mm

Available in Red, Blue, Yellow, Black and Green/Yellow

Approved Flammability to UL224 and FMVSS 302

2.4mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.51mm	2.4mm	20 metre	AHSB2.4BLK
Red	0.51mm	2.4mm	20 metre	AHSB2.4RED
Blue	0.51mm	2.4mm	20 metre	AHSB2.4BLU
Yellow	0.51mm	2.4mm	20 metre	AHSB2.4YEL
Green/Yellow	0.51mm	2.4mm	20 metre	AHSB2.4G/Y

3.2mm

Black	0.51mm	3.2mm	20 metre	AHSB3.2BLK
Red	0.51mm	3.2mm	20 metre	AHSB3.2RED
Blue	0.51mm	3.2mm	20 metre	AHSB3.2BLU
Yellow	0.51mm	3.2mm	20 metre	AHSB3.2YEL
Green/Yellow	0.51mm	3.2mm	20 metre	AHSB3.2G/Y

4.8mm

Black	0.51mm	4.8mm	10 metre	AHSB4.8BLK
Red	0.51mm	4.8mm	10 metre	AHSB4.8RED
Blue	0.51mm	4.8mm	10 metre	AHSB4.8BLU
Yellow	0.51mm	4.8mm	10 metre	AHSB4.8YEL
Green/Yellow	0.51mm	4.8mm	10 metre	AHSB4.8G/Y

6.4mm

Black	0.64mm	6.4mm	10 metre	AHSB6.4BLK
Red	0.64mm	6.4mm	10 metre	AHSB6.4RED
Blue	0.64mm	6.4mm	10 metre	AHSB6.4BLU
Yellow	0.64mm	6.4mm	10 metre	AHSB6.4YEL
Green/Yellow	0.64mm	6.4mm	10 metre	AHSB6.4G/Y

9.5mm

Black	0.64mm	9.5mm	10 metre	AHSB9.5BLK
Red	0.64mm	9.5mm	10 metre	AHSB9.5RED
Blue	0.64mm	9.5mm	10 metre	AHSB9.5BLU
Yellow	0.64mm	9.5mm	10 metre	AHSB9.5YEL
Green/Yellow	0.64mm	9.5mm	10 metre	AHSB9.5G/Y

12.7mm

Black	0.64mm	12.7mm	5 metre	AHSB12.7BLK
Red	0.64mm	12.7mm	5 metre	AHSB12.7RED
Blue	0.64mm	12.7mm	5 metre	AHSB12.7BLU
Yellow	0.64mm	12.7mm	5 metre	AHSB12.7YEL
Green/Yellow	0.64mm	12.7mm	5 metre	AHSB12.7G/Y

19.1mm

Black	0.76mm	19.1mm	5 metre	AHSB19.1BLK
Red	0.76mm	19.1mm	5 metre	AHSB19.1RED
Blue	0.76mm	19.1mm	5 metre	AHSB19.1BLU
Yellow	0.76mm	19.1mm	5 metre	AHSB19.1YEL
Green/Yellow	0.76mm	19.1mm	5 metre	AHSB19.1G/Y

25.4mm

Black	0.89mm	25.4mm	5 metre	AHSB25.4BLK
Red	0.89mm	25.4mm	5 metre	AHSB25.4RED
Blue	0.89mm	25.4mm	5 metre	AHSB25.4BLU
Yellow	0.89mm	25.4mm	5 metre	AHSB25.4YEL
Green/Yellow	0.89mm	25.4mm	5 metre	AHSB25.4G/Y

Heatshrink Sleeving Selection Packs

Colour	Inner Diameter	Pack Size	Part no.
All Colours	3.2mm	250mm x 4 cols x 3 lgths	AHSP3.2
All Colours	4.8mm	250mm x 4 cols x 3 lgths	AHSP4.8
All Colours	6.4mm	250mm x 4 cols x 3 lgths	AHSP6.4
All Colours	9.5mm	250mm x 4 cols x 3 lgths	AHSP9.5
All Colours	12.7mm	250mm x 4 cols x 3 lgths	AHSP12.7
All Colours	19.1mm	250mm x 4 cols x 3 lgths	AHSP19.1
All Colours	25.4mm	250mm x 4 cols x 3 lgths	AHSP25.4
All Colours	38.1mm	250mm x 4 cols x 3 lgths	AHSP38.1



Heatshrink Sleeving supplied in Dispenser Packs, Multipacks & Bulk Reels



Each pack contains 3 x 250 mm lengths in the above colours

Heatshrink Sleeving Bulk Reels and Earth Sleeving

Heatshrink Sleeving Bulk Reels

Thin Wall Polyolefin

2:1 Shrink Ratio - 2.4mm to 38.1mm

Available in Red, Blue, Yellow, Black and Green/Yellow

Approved Flammability to UL224 and FMVSS 302

2.4mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.51mm	2.4mm	150 metre	AHSR2.4BLK150
Red	0.51mm	2.4mm	150 metre	AHSR2.4RED150
Blue	0.51mm	2.4mm	150 metre	AHSR2.4BLU150
Yellow	0.51mm	2.4mm	150 metre	AHSR2.4YEL150

3.2mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.51mm	3.2mm	150 metre	AHSR3.2BLK150
Red	0.51mm	3.2mm	150 metre	AHSR3.2RED150
Blue	0.51mm	3.2mm	150 metre	AHSR3.2BLU150
Yellow	0.51mm	3.2mm	150 metre	AHSR3.2YEL150
Green/Yellow	0.51mm	3.2mm	150 metre	AHSR3.2G/Y150

4.8mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.51mm	4.8mm	150 metre	AHSR4.8BLK150
Red	0.51mm	4.8mm	150 metre	AHSR4.8RED150
Blue	0.51mm	4.8mm	150 metre	AHSR4.8BLU150
Yellow	0.51mm	4.8mm	150 metre	AHSR4.8YEL150
Green/Yellow	0.51mm	4.8mm	150 metre	AHSR4.8G/Y150

6.4mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.64mm	6.4mm	75 metre	AHSB6.4BLK75
Red	0.64mm	6.4mm	75 metre	AHSB6.4RED75
Blue	0.64mm	6.4mm	75 metre	AHSB6.4BLU75
Yellow	0.64mm	6.4mm	75 metre	AHSB6.4YEL75
Green/Yellow	0.64mm	6.4mm	75 metre	AHSB6.4G/Y75

9.5mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.64mm	9.5mm	75 metre	AHSR9.5BLK75
Red	0.64mm	9.5mm	75 metre	AHSR9.5RED75
Blue	0.64mm	9.5mm	75 metre	AHSR9.5BLU75
Yellow	0.64mm	9.5mm	75 metre	AHSR9.5YEL75
Green/Yellow	0.64mm	9.5mm	75 metre	AHSR9.5G/Y75

12.7mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.64mm	12.7mm	75 metre	AHSR12.7BLK75
Red	0.64mm	12.7mm	75 metre	AHSR12.7RED75
Blue	0.64mm	12.7mm	75 metre	AHSR12.7BLU75
Yellow	0.64mm	12.7mm	75 metre	AHSR12.7YEL75
Green/Yellow	0.64mm	12.7mm	75 metre	AHSR12.7G/Y75

19.1mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.76mm	19.1mm	75 metre	AHSR19.1BLK75
Red	0.76mm	19.1mm	75 metre	AHSR19.1RED75
Blue	0.76mm	19.1mm	75 metre	AHSR19.1BLU75
Yellow	0.76mm	19.1mm	75 metre	AHSR19.1YEL75
Green/Yellow	0.76mm	19.1mm	75 metre	AHSR19.1G/Y75

25.4mm


Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Black	0.89mm	25.4mm	30 metre	AHSR25.4BLK30
Red	0.89mm	25.4mm	30 metre	AHSR25.4RED30
Blue	0.89mm	25.4mm	30 metre	AHSR25.4BLU30
Yellow	0.89mm	25.4mm	30 metre	AHSR25.4YEL30
Green/Yellow	0.89mm	25.4mm	30 metre	AHSR25.4G/Y30

Earth Sleeving


Standard PVC Sleeving

Inner Dimension range from 2mm to 6mm

Colour	Size	Wall Thickness	Inner Diameter	Pack Size	Part no.
Green/Yellow	2mm	0.5mm	2mm	100 metre	AES2
Green/Yellow	3mm	0.5mm	3mm	100 metre	AES3
Green/Yellow	4mm	0.5mm	4mm	100 metre	AES4
Green/Yellow	5mm	0.5mm	5mm	100 metre	AES5
Green/Yellow	6mm	0.5mm	6mm	100 metre	AES6



Neoprene Sleeve Expansion Tool
ANST
See Tooling Catalogue for details



Heatshrink Sleeving supplied in Bulk Reels



Available in
2.0-6.0mm diameters

Neoprene Sleeving, Braided Sleeving, Grommet Strip and Spirap™

Neoprene Sleeving

Made from extruded polychloroprene rubber
Available in Red, Blue, Black and Yellow
Size range 1.2mm to 10.0mm

2.4mm

Colour	Inner Diameter	Length	Pack Quantity	Part no.
Black	1.2-2.4mm	20mm	500	ANS12/20BLK
Blue	1.2-2.4mm	20mm	500	ANS12/20BLU
Red	1.2-2.4mm	20mm	500	ANS12/20RED
Yellow	1.2-2.4mm	20mm	500	ANS12/20YEL



Available in 1.2-10.0mm inner diameters

3.0mm

Colour	Inner Diameter	Length	Pack Quantity	Part no.
Black	1.5-3.0mm	20mm	500	ANS15/20BLK
Blue	1.5-3.0mm	20mm	500	ANS15/20BLU
Red	1.5-3.0mm	20mm	500	ANS15/20RED
Yellow	1.5-3.0mm	20mm	500	ANS15/20YEL

4.0mm

Colour	Inner Diameter	Length	Pack Quantity	Part no.
Black	2.0-4.0mm	20mm	250	ANS20/20BLK
Blue	2.0-4.0mm	20mm	250	ANS20/20BLU
Red	2.0-4.0mm	20mm	250	ANS20/20RED
Yellow	2.0-4.0mm	20mm	250	ANS20/20YEL

6.0mm

Colour	Inner Diameter	Length	Pack Quantity	Part no.
Black	3.0-6.0mm	25mm	250	ANS30/25BLK
Blue	3.0-6.0mm	25mm	250	ANS30/25BLU
Red	3.0-6.0mm	25mm	250	ANS30/25RED
Yellow	3.0-6.0mm	25mm	250	ANS30/25YEL

10.0mm

Colour	Inner Diameter	Length	Pack Quantity	Part no.
Black	5.0-10.0mm	25mm	100	ANS50/25BLK
Blue	5.0-10.0mm	25mm	100	ANS50/25BLU
Red	5.0-10.0mm	25mm	100	ANS50/25RED
Yellow	5.0-10.0mm	25mm	100	ANS50/25YEL

Grommet Strip

Made from Polyester in Natural colour only
Supplied in 10 metre lengths
Plate thickness range from 1.0mm to 3.2mm

Colour	Chassis Thickness	Pack Size	Part no.
Natural	1.0-1.2mm	10 metres	AGS1
Natural	1.6-2.0mm	10 metres	AGS1.6
Natural	2.4-3.2mm	10 metres	AGS2.4



Available in plate thickness range from 1.0-3.2mm

Spirap™ Spiral Band

Made in Polythene for maximum strength and insulation
Available in Natural and Black
Supplied in 10 metre packs
Bundle Range from 15mm to 100mm

Colour	Size	Inner Diameter	Bundle Diameter	Band Width	Pack Size	Part no.
Natural	15-18mm	1.5mm	Range 15-18mm	4mm	10 metres	ASB1.5N
Natural	4-50mm	4.1mm	Range 4-50mm	7mm	10 metres	ASB4N
Natural	7.5-60mm	10.0mm	Range 7.5-60mm	11.4mm	10 metres	ASB7.5N
Natural	15-100mm	19.0mm	Range 15-100mm	18.2mm	10 metres	ASB15N
Black	15-18mm	1.5mm	Range 15-18mm	4mm	10 metres	ASB1.5B
Black	4-50mm	4.1mm	Range 4-50mm	7mm	10 metres	ASB4B
Black	7.5-60mm	10.0mm	Range 7.5-60mm	11.4mm	10 metres	ASB7.5B
Black	15-100mm	19.0mm	Range 15-100mm	18.2mm	10 metres	ASB15B



Available in Bundle Range from 15.0-130.0mm

Braided Sleeving

Made from Polyester
Self Extinguishing to UL 94V2
Grey or Black
Size range 6mm to 50mm diameter
Supplied in 10 metre packs

Colour	Diameter	Pack Size	Part no.
Grey	6mm	10 metres	ABS6GRY
Grey	10mm	10 metres	ABS10GRY
Grey	15mm	10 metres	ABS15GRY
Grey	20mm	10 metres	ABS20GRY
Grey	25mm	10 metres	ABS25GRY
Grey	30mm	10 metres	ABS30GRY
Grey	40mm	10 metres	ABS40GRY
Grey	50mm	10 metres	ABS50GRY
Black	6mm	10 metres	ABS6BLK
Black	10mm	10 metres	ABS10BLK
Black	15mm	10 metres	ABS15BLK
Black	20mm	10 metres	ABS20BLK
Black	25mm	10 metres	ABS25BLK
Black	30mm	10 metres	ABS30BLK
Black	40mm	10 metres	ABS40BLK
Black	50mm	10 metres	ABS50BLK



Available in 6.0-50.0mm diameters

Braided Sleeving Bulk Reels

Made from Polyester
Self Extinguishing to UL 94V2
Grey or Black
Size range 6mm to 50mm diameter

Colour	Diameter	Pack Size	Part no.
Grey	6mm	100 metres	ABS6GRY-100
Grey	10mm	100 metres	ABS10GRY-100
Grey	15mm	50 metres	ABS15GRY-50
Grey	20mm	25 metres	ABS20GRY-25
Grey	25mm	25 metres	ABS25GRY-25
Grey	30mm	25 metres	ABS30GRY-25
Grey	40mm	25 metres	ABS40GRY-25
Grey	50mm	25 metres	ABS50GRY-25
Black	6mm	100 metres	ABS6BLK-100
Black	10mm	100 metres	ABS10BLK-100
Black	15mm	50 metres	ABS15BLK-50
Black	20mm	25 metres	ABS20BLK-25
Black	25mm	25 metres	ABS25BLK-25
Black	30mm	25 metres	ABS30BLK-25
Black	40mm	25 metres	ABS40BLK-25
Black	50mm	25 metres	ABS50BLK-25



Available in 6.0-50.0mm diameters



Braided Sleeving supplied in Bulk Reels

PVC Sleeving

PVC Sleeving

Non Shrink oversleeving

Operating Temperature -20°C to +70°C

Available in Red, Black, Blue, Yellow, Green, White and Brown

2mm

Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Red	0.5mm	2.0mm	100 metre	APVC2R
Black	0.5mm	2.0mm	100 metre	APVC2B
Blue	0.5mm	2.0mm	100 metre	APVC2BL
Yellow	0.5mm	2.0mm	100 metre	APVC2Y
Green	0.5mm	2.0mm	100 metre	APVC2G
White	0.5mm	2.0mm	100 metre	APVC2W
Brown	0.5mm	2.0mm	100 metre	APVC2BRN

3mm

Red	0.5mm	3.0mm	100 metre	APVC3R
Black	0.5mm	3.0mm	100 metre	APVC3B
Blue	0.5mm	3.0mm	100 metre	APVC3BL
Yellow	0.5mm	3.0mm	100 metre	APVC3Y
Green	0.5mm	3.0mm	100 metre	APVC3G
White	0.5mm	3.0mm	100 metre	APVC3W
Brown	0.5mm	3.0mm	100 metre	APVC3BRN

4mm

Red	0.5mm	4.0mm	100 metre	APVC4R
Black	0.5mm	4.0mm	100 metre	APVC4B
Blue	0.5mm	4.0mm	100 metre	APVC4BL
Yellow	0.5mm	4.0mm	100 metre	APVC4Y
Green	0.5mm	4.0mm	100 metre	APVC4G
White	0.5mm	4.0mm	100 metre	APVC4W
Brown	0.5mm	4.0mm	100 metre	APVC4BRN

5mm

Red	0.5mm	5.0mm	100 metre	APVC5R
Black	0.5mm	5.0mm	100 metre	APVC5B
Blue	0.5mm	5.0mm	100 metre	APVC5BL
Yellow	0.5mm	5.0mm	100 metre	APVC5Y
Green	0.5mm	5.0mm	100 metre	APVC5G
White	0.5mm	5.0mm	100 metre	APVC5W
Brown	0.5mm	5.0mm	100 metre	APVC5BRN

6mm

Red	0.5mm	6.0mm	100 metre	APVC6R
Black	0.5mm	6.0mm	100 metre	APVC6B
Blue	0.5mm	6.0mm	100 metre	APVC6BL
Yellow	0.5mm	6.0mm	100 metre	APVC6Y
Green	0.5mm	6.0mm	100 metre	APVC6G
White	0.5mm	6.0mm	100 metre	APVC6W
Brown	0.5mm	6.0mm	100 metre	APVC6BRN

8mm

Red	0.5mm	8.0mm	100 metre	APVC8R
Black	0.5mm	8.0mm	100 metre	APVC8B
Blue	0.5mm	8.0mm	100 metre	APVC8BL
Yellow	0.5mm	8.0mm	100 metre	APVC8Y
Green	0.5mm	8.0mm	100 metre	APVC8G
White	0.5mm	8.0mm	100 metre	APVC8W
Brown	0.5mm	8.0mm	100 metre	APVC8BRN

10mm

Red	0.5mm	10.0mm	100 metre	APVC10R
Black	0.5mm	10.0mm	100 metre	APVC10B
Blue	0.5mm	10.0mm	100 metre	APVC10BL
Yellow	0.5mm	10.0mm	100 metre	APVC10Y
Green	0.5mm	10.0mm	100 metre	APVC10G
White	0.5mm	10.0mm	100 metre	APVC10W
Brown	0.5mm	10.0mm	100 metre	APVC10BRN

12mm


Colour	Wall Thickness	Inner Diameter	Pack Size	Part no.
Red	0.5mm	12.0mm	100 metre	APVC12R
Black	0.5mm	12.0mm	100 metre	APVC12B
Blue	0.5mm	12.0mm	100 metre	APVC12BL
Yellow	0.5mm	12.0mm	100 metre	APVC12Y
Green	0.5mm	12.0mm	100 metre	APVC12G
White	0.5mm	12.0mm	100 metre	APVC12W
Brown	0.5mm	12.0mm	100 metre	APVC12BRN

15mm

Red	0.5mm	15.0mm	100 metre	APVC15R
Black	0.5mm	15.0mm	100 metre	APVC15B
Blue	0.5mm	15.0mm	100 metre	APVC15BL
Yellow	0.5mm	15.0mm	100 metre	APVC15Y
Green	0.5mm	15.0mm	100 metre	APVC15G
White	0.5mm	15.0mm	100 metre	APVC15W
Brown	0.5mm	15.0mm	100 metre	APVC15BRN

20mm

Red	0.5mm	20.0mm	100 metre	APVC20R																			
Black	0.5mm	20.0mm	100 metre	APVC20B																			
Blue	0.5mm	20.0mm	100 metre <td APVC20BL	Yellow	0.5mm	20.0mm	100 metre	APVC20Y	Green	0.5mm	20.0mm	100 metre	APVC20G	White	0.5mm	20.0mm	100 metre	APVC20W	Brown	0.5mm	20.0mm	100 metre	APVC20BRN
Yellow	0.5mm	20.0mm	100 metre	APVC20Y																			
Green	0.5mm	20.0mm	100 metre	APVC20G																			
White	0.5mm	20.0mm	100 metre	APVC20W																			
Brown	0.5mm	20.0mm	100 metre	APVC20BRN																			



PVC Sleeving supplied in 100 metre lengths

The Ampliversal Range



Terminals



HTS Heavy Duty
Connectors



Sleeving
Products



Tooling



Overview



Cable Glands



Cable Ties
& Bases



Schrack
PT Relays



Industrial
Control Stations

Ampliversal

TERMINALS • TOOLING • CABLE ACCESSORIES

Dunlop Road, Hunt End, Redditch, Worcs. B97 5XP

Freephone: 0800 3169991 Freefax: 0800 3169992

E-mail: ampliversal@tycoelectronics.com

tyco
Electronics