



10 mm²/10 mm wide
16 mm²/12 mm wide
35 mm²/16 mm wide
70 mm²/24 mm wide

4 mm²/6 mm wide

6 mm²/6 mm wide

Type	Part No.	Std. Pack	Type	Part No.	Std. Pack	Type	Part No.	Std. Pack
Marking strips, unmarked			Marking strips, unmarked			10 mm²/10 mm Baubreite		
9705 A/6/10	04.242.6053.0	25	9705 A/8/10	04.242.8053.0	25	for 5 blocks		
Marking strips, marked			Marking strips, marked			9705 A/5/10/5 B 04.842.5553.0 25		
9705A/6/9 B 1 - 9	04.842.5953.0	25	9705A/8/9 B 1 - 9	04.842.7953.0	25	16 mm²/12 mm wide		
9705A/6/10 B *	04.842.6053.0	25	9705A/8/10 B *	04.842.8053.0	25	for 5 blocks		
9705A/6/10 B 1 - 10	04.846.0153.0	25	9705A/8/10 B 1 - 10	04.848.0153.0	25	9705 A/6/10/5 B 04.842.6553.0 25		
9705A/6/10 B 11 - 20	04.846.0253.0	25	9705A/8/10 B 11 - 20	04.848.0253.0	25	35 mm²/16 mm wide		
9705A/6/10 B 21 - 30	04.846.0353.0	25	9705A/8/10 B 21 - 30	04.848.0353.0	25	for 5 blocks		
9705A/6/10 B 31 - 40	04.846.0453.0	25	9705A/8/10 B 31 - 40	04.848.0453.0	25	9705 A/8/10/5 B 04.842.8553.0 25		
9705A/6/10 B 41 - 50	04.846.0553.0	25	9705A/8/10 B 41 - 50	04.848.0553.0	25	70 mm²/24 mm wide		
9705A/6/10 B 51 - 60	04.846.0653.0	25	9705A/8/10 B 51 - 60	04.848.0653.0	25	for 4 blocks		
9705A/6/10 B 61 - 70	04.846.0753.0	25	9705A/8/10 B 61 - 70	04.848.0753.0	25	9705 A/8/10/5 B 04.842.8553.0 25		
9705A/6/10 B 71 - 80	04.846.0853.0	25	9705A/8/10 B 71 - 80	04.848.0853.0	25			
9705A/6/10 B 81 - 90	04.846.0953.0	25	9705A/8/10 B 81 - 90	04.848.0953.0	25			
9705A/6/10 B 91 - 100	04.846.1053.0	25	9705A/8/10 B 91 - 100	04.848.1053.0	25			
9705A/6/10 B SLZ	04.856.0053.0	25	9705A/8/10 B SLZ	04.858.0053.0	25			
9705A/6/10 B ERDZ	04.856.0153.0	25	9705A/8/10 B ERDZ	04.858.0153.0	25			
9705A/6/10 B +	04.856.0253.0	25	9705A/8/10 B +	04.858.0253.0	25			
9705A/6/10 B -	04.856.0353.0	25	9705A/8/10 B -	04.858.0353.0	25			
9705A/6/10 B L1	04.856.0453.0	25	9705A/8/10 B L1	04.858.0453.0	25			
9705A/6/10 B L2	04.856.0553.0	25	9705A/8/10 B L2	04.858.0553.0	25			
9705A/6/10 B L3	04.856.0653.0	25	9705A/8/10 B L3	04.858.0653.0	25			
9705A/6/10 B PE	04.856.0753.0	25	9705A/8/10 B PE	04.858.0753.0	25			
9705A/6/10 B SL	04.856.3153.0	25	9705A/8/10 B SL	04.858.3153.0	25			
9705A/6/10 B N	04.856.3253.0	25	9705A/8/10 B N	04.858.3253.0	25			
9705A/6/10 B F1	04.856.0953.0	25	9705A/8/10 B F1	04.858.0953.0	25			
9705A/6/10 B F2	04.856.1053.0	25	9705A/8/10 B F2	04.858.1053.0	25			
9705A/6/10 B L1L2L3NPE..	04.856.0853.0	25	9705A/8/10 B L1L2L3NPE..	04.858.0853.0	25			
with enlarged marking area								
9705 AL/6/10	04.242.6353.0	25						
* Custom marking upon request			* Custom marking upon request					