


15 Amp Hospital Grade



- ~ Designed to meet the special requirements for hospital, institutional and chronic care use.
- ~ All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- ~ Comes with hospital grade “Green Dot” white receptacles, line cord and plug.
- ~ Heavy-duty white hospital grade receptacles, securely fastened onto the housing and interconnected with solidly bonded bus bars. All bus bars are double connected with convection pressure sensitive clamp and safety screw (also, perfect for ground sensitive audio applications).
- ~ An additional grounding screw is provided on the case for any further external grounding requirements.
- ~ Heavy-duty 14 gauge power cord – 14/3 SJT with “Green Dot” hospital grade clear molded plug.
- ~ Unit exceeds NEMA requirements for low leakage ground return and for withstanding impact or continuous physical shock without loss of grounding path continuity when plugged into hospital grade source receptacles.
- ~ Includes 15A, 125VAC resettable circuit breaker to prevent accidental line overload.
- ~ Mounting feet with keyhole slots provide for work station mounting if desired.
- ~ CSA certified – hospital grade.
- ~ UL 1363 listed.

15 Amp Hospital Grade



Part No.	Outlets	Cord Length	Dimensions (Inches)	Electrical Rating	Shipping Weight
1584T4DH6	4	6'	11 x 2 x 2	125VAC /15A	2.5 lbs
1584T4DH15	4	15'	11 x 2 x 2	125VAC/15A	3.5 lbs
1584T6DH6	6	6'	14 x 2 x 2	125VAC /15A	2.7 lbs
1584T6DH15	6	15'	14 x 2 x 2	125VAC /15A	3.7 lbs
1584T8DH6	8	6'	17 x 2 x 2	125VAC /15A	2.9 lbs
1584T8DH15	8	15'	17 x 2 x 2	125VAC /15A	3.9 lbs