

CHERRY MX BOARD 1.0 BACKLIGHT



Models may vary from the image shown

The ideal keyboard for avid writers complete with MX switches and palm rest

The CHERRY MX BOARD 1.0 BACKLIGHT – fast, precise, proven CHERRY quality.

Durable CHERRY MX switches with consistent linear or tactile operating feel and the support of the palm rest provide comfort and ergonomics when working. High-speed key recognition accurately captures every keystroke, even with fast typing.

Sturdy mounting feet enable a perfect adjustment in 3 steps with a non-slip grip. The adjustable, white key illumination means the keys can be read clearly even in challenging visibility conditions.

All inputs are reliably and precisely executed, and input errors are prevented thanks to anti-ghosting and full n-key rollover.

Frequent number inputs can be performed easily via the numeric keypad; the switchable Win key lockout enables the keyboard to be used for pleasure on the computer after work as well.

The CHERRY MX BOARD 1.0 BACKLIGHT - the high-performance keyboard for people who type quickly or write a lot.

Key benefits

- Anti-ghosting - no inputting errors
- Corded keyboard with CHERRY MX switches and palm rest
- CHERRY MX technology - Gold Crosspoint precision switches for all keys "Made in Germany"
- Uncompromisingly fast thanks to CHERRY MX and high-speed key recognition
- Abrasion-resistant, laser-etched keycaps
- Full N-Key rollover - all keys are read simultaneously
- WIN key lockout
- Dimmable, white backlighting with several lighting modes
- Additional feet for non-slip grip and custom height adjustment in 3 steps
- Illuminated USB plug and elegant logo application

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

black

Key colour:

black

Weight (product):

approx. 1165 g

Total weight (with packaging):

approx. 1510 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 50°C



Current Consumption:

max. 500 mA

Interface:

- USB

Product approvals:

- CE 
- KCC 
- WHQL

System requirements:

- USB connection

Delivery Volume:

- CHERRY MX BOARD 1.0 BACKLIGHT
- Wrist rest
- Operating instructions in hard copy

Dimensions (product):

approx. 470 x 165 x 25 mm (keyboard), approx. 470 x 95 x 25 mm (wrist rest)

Packaging dimensions:

approx. 520 x 200 x 48 mm

Keyboard:

- Key technology: Product dependant, see table "Models"
- Service life, standard key: > 50 million key operations
- Operation characteristics: Product dependant, see table "Models"
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: 105+4
- Number of additional keys: 4

Packaging Unit:

- Number of products in the master package: 7

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.


Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Key technology	Operation characteristics ¹
1	MX BOARD 1.0 BACKLIGHT	G80-3816LWBCH-2	4025112089923	Switzerland	MX-Silent	RED SWITCH SILENT Linear (45 cN)
2	MX BOARD 1.0 BACKLIGHT	G80-3816LWBDE-2	4025112089169	Germany	MX-Silent	RED SWITCH SILENT Linear (45 cN)
3	MX BOARD 1.0 BACKLIGHT	G80-3816LWBES-2	4025112089190	Spain	MX-Silent	RED SWITCH SILENT Linear (45 cN)
4	MX BOARD 1.0 BACKLIGHT	G80-3816LWBFR-2	4025112089176	France	MX-Silent	RED SWITCH SILENT Linear (45 cN)
5	MX BOARD 1.0 BACKLIGHT	G80-3816LWBGB-2	4025112089183	UK	MX-Silent	RED SWITCH SILENT Linear (45 cN)
6	MX BOARD 1.0 BACKLIGHT	G80-3816LWBPN-2	4025112089206	Pan-Nordic	MX-Silent	RED SWITCH SILENT Linear (45 cN)
7	MX BOARD 1.0 BACKLIGHT	G80-3816LXBCH-2	4025112089916	Switzerland	MX	BROWN SWITCH Pressure point (55cN)
8	MX BOARD 1.0 BACKLIGHT	G80-3816LXBDE-2	4025112089077	Germany	MX	BROWN SWITCH Pressure point (55cN)
9	MX BOARD 1.0 BACKLIGHT	G80-3816LXBES-2	4025112089107	Spain	MX	BROWN SWITCH Pressure point (55cN)
10	MX BOARD 1.0 BACKLIGHT	G80-3816LXBFR-2	4025112089084	France	MX	BROWN SWITCH Pressure point (55cN)
11	MX BOARD 1.0 BACKLIGHT	G80-3816LXBGB-2	4025112089091	UK	MX	BROWN SWITCH Pressure point (55cN)
12	MX BOARD 1.0 BACKLIGHT	G80-3816LXBPN-2	4025112089114	Pan-Nordic	MX	BROWN SWITCH Pressure point (55cN)

1 Operation characteristics:

• **BROWN SWITCH Pressure point (55cN)**



• **RED SWITCH SILENT Linear (45 cN)**

