



APC Replacement Battery Cartridge #55

Part Number: RBC55

[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	816
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

Physical

Net Weight	24.27 KG
Maximum Height	173.00 mm
Maximum Width	142.00 mm
Maximum Depth	183.00 mm
Shipping Weight	26.68 KG
Shipping Width	295.00 mm
Shipping Height	277.00 mm
Shipping Depth	538.00 mm
Color	Black
Units per Pallet	18.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
------	-----------

REACH	REACH: Contains No SVHCs
-------	--------------------------