



Inductor

Order code	TCK-059
Inductance	2.2 μ H \pm 20% (at 1 kHz / 250 mV)
Rated current	3.8 A max.
DCR	25 m Ω
Operating temperature	-40 to +125°C

Impedance curve



Dimensions [mm]

A	5.2 \pm 0.5
B	5.8 \pm 0.6
C	4.5 \pm 0.55
D	2.3 typ.
E	5.5
F	2.15
G	1.7

