


Common mode choke

Order code	TCK-050
Inductance	Pin 1-2: 325 μ H \pm 35% (at 100 kHz / 100 mV) Pin 3-4: 325 μ H \pm 35% (at 100 kHz / 100 mV)
Rated current	3.3 A max.
DCR	Pin 1-2: 35 m Ω Pin 3-4: 35 m Ω
Rated voltage	500 VDC
Operating temperature	-40 to +105°C

Impedance curve



Dimensions [mm]

A	11.5 max.
B	11.5 max.
C	8.8 max.
D	2.5 min.
E	7.62 \pm 0.2
F	7.62 \pm 0.2
G	\varnothing 0.6 \pm 0.1

