

KUBO5-W

5.25" Compact design two-way
loudspeaker, white




KUBO5 is a 5.25" two-way loudspeaker with integrated bass reflex port providing a dynamic and fast bass response. The unseen original and timeless KUBO cabinet produces 80 watts dynamic power at 8 ohms. Multiple KUBO loudspeakers can easily be daisy chained via the in & link connection with euroblock connectors.

The K-Mount bracket & fixing K-bolts offer a safe and comfortable loudspeaker hook-up. The easy cable management and 140° vertical or horizontal mounting possibility allows you to install the KUBO5 everywhere on any type of wall or ceiling. The intuitive end-caps are very installer-friendly and are kept in place by 14 integrated strong neodymium magnets, hiding all connections and bracket hardware on both sides. KUBO will blend audio in with any kind of interior and architect designed environment.

TECHNICAL SPECIFICATIONS

height in mm	155	width in mm	164
depth in mm	136	loudspeaker system	2-way
woofer size in inch	5.25	woofer cone material	coated paper
tweeter size in inch	1	mounting system	U-bracket
colour	black / white	impedance (ohms)	8
low impedance dynamic power in watts	80	low impedance RMS power in watts	50
SPL 1W/1m in dB	92	max SPL 1m in dB	106
frequency response in Hz	94 - 20K	main construction material	ABS plastic
grille main material	steel	IP rating	40
Horizontal dispersion angle 1000 Hz	180°	Vertical dispersion angle 1000 Hz	180°
closest RAL colour (subject to deviations)	RAL9016 (W) / RAL9011 (BL)	Net weight product (kg)	1.7

POLAR PLOTS



MORE PICTURES



ACCESSORIES



LRAPRE-W

Premium light rail adaptor KUBO3/5,SDQ5P,OVO5, pack of 2

LRBAS-W

Basic light rail adaptor KUBO3/5, SDQ5P, OVO5, pack of 10