


## A-S

### Non-Replaceable Probe - Epoxy Mount

Product Family: A-S



#### Mechanical:

**Test Center (mil):** 50

**Test Center (mm):** 1.27

**Overall Length (mil):** 230

**Overall Length (mm):** 5.84

**Full Travel (mil):** 30

**Full Travel (mm):** 0.76

**Recommended Travel (mil):** 20

**Recommended Travel (mm):** 0.51

**Rec. Mounting Hole Size (mil):** 38

**Rec. Mounting Hole Size (mm):** 0.97

**Recommended Drill Size:** #62 or 0.97 mm

#### Thermal:

**Max Operating Temp (°C):** 150

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 2

**Average DC Resistance lower than (mOhm):** 30

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu or Brass, Gold plated

**Barrel Material:** Brass, Gold plated

**Ball Material:** Stainless Steel

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 0.70 (20.00) - 1.30 (37.00) - Stainless Steel, Gold plated

#### Additional information:


The recommended hole is .0380(#62 drill) for epoxy mounting

TIPS:

Tip Materials: BeCu

Tips:

A-S-C



A-S-R



A-S-V

