


P2532

Non-Replaceable Probe - Epoxy Mount

Product Family: Pylon



Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 1.00 (28.00) - 2.30 (65.00) - Stainless Steel, Gold plated

Mechanical:

Test Center (mil): 156

Test Center (mm): 3.96

Overall Length (mil): 812

Overall Length (mm): 20.62

Full Travel (mil): 139

Full Travel (mm): 3.53

Recommended Travel (mil): 93

Recommended Travel (mm): 2.36

Rec. Mounting Hole Size (mil): 94.5

Rec. Mounting Hole Size (mm): 2.40

Recommended Drill Size: #41 or 2.40 mm

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 5

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over hard Nickel

Barrel Material: Brass, Gold plated

Ball Material: Gold plated, Stainless Steel

TIPS:

Tip Materials: BeCu

Tips:

P2532-1



P2532-2

