


P2662A

Pylon Probe

Product Family: Pylon



Mechanical:

Test Center (mil): 50

Test Center (mm): 1.27

Overall Length (mil): 710

Overall Length (mm): 18.03

Full Travel (mil): 90

Full Travel (mm): 2.29

Recommended Travel (mil): 67

Recommended Travel (mm): 1.70

Thermal:

Max Operating Temp (°C): 85

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 3

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over hard Nickel

Barrel Material: Phosphor Bronze, Gold plated

Ball Material: Stainless Steel

Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 0.70 (2.00) - 1.70 (48.00) - BeCu, Silver plated

Alternate - 0.60 (17.00) - 2.50 (71.00) - BeCu, Silver plated

Body Type

Straight


Pylon Bend

TIPS:


Tip Materials: BeCu, Gold plated

Tips:


P2662-2V




P2662-1R



P2662-1Q



P2662-1C



Related Products:

S2662A-3ED

