


P3325

Feed Through Probe

Product Family: Pylon



Mechanical:

Test Center (mil): 125

Test Center (mm): 3.18

Overall Length (mil): 645

Overall Length (mm): 16.38

Full Travel (mil): 100

Full Travel (mm): 2.54

Recommended Travel (mil): 66

Recommended Travel (mm): 1.68

Thermal:

Max Operating Temp (°C): 105

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 10

Average DC Resistance lower than (mOhm): 10

Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 5.00 (142.00) - 8.30 (235.00) - Music Wire

Materials & Finishes:

Plunger Material: Hardened BeCu, Gold plated

Barrel Material: Brass

TIPS:

Tip Materials: BeCu

Tips:

P3325_0



P3325_1

