

# EDIFIER®

## R1280T

Technology. Style. Utility. You can have it all.

Equipped with dual RCA inputs the Studio 1280T can produce up to 42W RMS of audio output. A 4 inch bass driver and front facing bass reflex port ensures bass notes are robust and rich in sound.

Connect to multiple devices and personalize your listening experience with the bass and treble adjustment dials located on the active speaker. A remote control also controls the volume and mute function.



**42**  
watts  
**R.M.S**  
TOTAL POWER OUTPUT



### Features

- Active bookshelf speaker system with 42W total power output
- Dual RCA inputs for connectivity to multiple audio sources
- Bass, treble and master volume dials located on the side panel
- Wireless remote control for volume adjustment and mute
- Calibrated, flared front-facing bass reflect port
- 100% MDF wooden enclosures to minimize acoustic resonance
- Universal 100V-240V power supply

### Specifications

|                       |  |
|-----------------------|--|
| Power Output          | : RMS 21W × 2                            |
| Signal to noise ratio | : ≥85dBA                                 |
| Frequency response    | : 75Hz~18KHZ                             |
| Input sensitivity     | : LPC: 750mV ± 50mV<br>Aux: 550mV ± 50mV |
| Input type            | : RCA - 3.5mm Auxiliary, RCA             |
| Bass driver           | : 4", 6Ω, with bass reflection port      |
| Treble driver         | : 13mm silk dome tweeter, 4Ω             |
| EAN code              | : 6923520265084 (UK)                     |



Disclaimer: All specifications are subject to change without notice

[www.edifier.com](http://www.edifier.com)

A Passion for Sound