



Ultra Low Profile Power Resistors

WDBR-UL Series

- Ultra low profile thick-film on steel
- Up to 7kW peak power
- Single fixing heatsink mountable
- Ideal for dynamic braking, inrush limit and snubber circuits
- Choice of flying lead or solder terminations
- Low inductance design
- High isolation, even after failsafe overload fusing
- RoHS compliant, non-flammable construction
- UL508 certified - UL file E238661



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		WDBR1UL	WDBR2UL	WDBR3UL	WDBR5UL	WDBR7UL
Resistance range ⁵	ohms	12, 15, 20, 22, 25, 47, 50, 100, 150				
Resistance tolerance	%	10				
Pulse power rating ¹	kW	1.5	2.0	3.5	5.0	7.0
Power rating on heatsink ²	W	170	190	240	250	260
Power rating on fan-cooled heatsink ³	W	660	740	850	950	1410
TCR	ppm/°C	< +600				
Maximum element temperature	°C	450				
Ambient temperature range (heatsink)	°C	-55 to +200				
Dielectric withstand ⁴	V (dc/ac peak)	2500				
Inductance (typical)	µH	<3	<4	<5	<5	<6

Notes:

1. For details of pulse condition see Fig. 1 in Performance Data.
2. Mounted on a 0.53°C/W heatsink with no forced air cooling, air temperature 25°C.
3. Mounted on a 0.53°C/W heatsink with 5m/s forced air cooling, air temperature 25°C.
4. Based on 100% production test, duration 2s minimum
5. Other ohmic values upon request

Physical Data

Dimensions in mm, weight without terminations in g									
	L ±0.25	W ±0.25	t ±0.1	ΦD nom	a ±1	b ±1	c ±1	Wt. nom	
WDBR1UL	49.3	35.9	0.9	5.3	3.2	4.2	17.6	4.2	12.6
WDBR2UL	61	40.6			5.5	19.7	5.5	17.1	
WDBR3UL	101.6	70	14.5		24.8	10.1	50.8		
WDBR5UL	122	70	15.3		27	8.6	101.2		
WDBR7UL	152.4	101.6	1.5		39.3	10.7	11.8	181.8	



Fixing hole is located centrally.
In addition to the central fixing hole, WDBR7UL has two corner holes. These are present for manufacturing purposes only and should not be used as fixing holes.

Construction

A high integrity dielectric layer is applied to a machined stainless steel substrate. Thick-film conductor and resistor patterns are printed and fired, then protected with a high temperature overglaze. The termination pads are tinned with solder and optional leads are soldered on.



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

WDBR-UL Series

Terminations

The following termination options are available

Option	Code	Nominal Dimensions (mm)															
Solder pad only ¹	I		<table border="1"> <thead> <tr> <th>WDBR-UL Size</th> <th>1 & 2</th> <th>3</th> <th>5 & 7</th> </tr> </thead> <tbody> <tr> <td>Pad Length, PL</td> <td>8.8</td> <td>8.1</td> <td>9.1</td> </tr> <tr> <td>Pad Width, PW</td> <td>5</td> <td>8.1</td> <td>6.1</td> </tr> </tbody> </table>			WDBR-UL Size	1 & 2	3	5 & 7	Pad Length, PL	8.8	8.1	9.1	Pad Width, PW	5	8.1	6.1
			WDBR-UL Size	1 & 2	3	5 & 7											
Pad Length, PL	8.8	8.1	9.1														
Pad Width, PW	5	8.1	6.1														
Flying leads, UL3134/5, 40A, 600V	L																

Notes:

1. Two options exist for solder type. The standard is SnAg (965C) which is Pb-free and the second (HT) is high temperature HMP alloy which is Pb-bearing. Both are RoHS compliant, but the second relies on the RoHS exemption for high temperature solders and is targeted at specialist high temperature applications.

Thermal Performance

	$\Delta R\%$	Maximum
Pulsed load at full pulse power rating 50,000 cycles (see Fig 1) Mounted on a 0.53°C/W heatsink with 5m/s forced air cooling, air temperature 25°C.		5
Derating at heatsink temperatures >160°C		See Fig. 2



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Application Notes

A heatsink with thermal resistance $\leq 0.53^{\circ}\text{C}/\text{W}$ will enable the component to operate at its continuous power rating. Sufficient thermal grease (e.g. Dow Corning DC340) to give void-free coverage, or a 0.5mm thick compliant thermal pad (e.g. T Global TG-X) should be used and the heatsink should have a surface finish of $<6.3\mu\text{m}$ with flatness of $<0.05\text{mm}$. The resistor should be mounted using an appropriate bolt as listed in the table below. This should be tightened so as to bring the whole area of the steel substrate into intimate contact with the heatsink. The unmounted part is slightly bowed so that the centre is above the edges. Inadequate tightening will leave the centre out of contact with the heatsink, whilst over tightening can cause the edges to rise. The tightening torque required will depend on the fixings and heatsink used, but typical figures are given for guidance. WDBR-UL resistors will fail safe (open circuit) under overload fault conditions and still maintain a 1kV dielectric withstand.

	Bolt Size	Typical Tightening Torque (Nm)
WDBR1UL	M3	2
WDBR2UL	M5	2.5
WDBR3UL	M5	2.5
WDBR5UL	M5	3.5
WDBR7UL	M5	4

WDBR resistors may be customised in various ways including:

- Alternative shapes and dimensions up to 406mm x 406mm
- Integration of temperature measurement elements
- Alternative ohmic values, tolerance & TCR
- Increased dielectric withstand voltage
- Custom braking resistors with UL approval

For a full Applications Note for dynamic braking see <http://www.ttelectronics.com/themes/ttelectronics/datasheets/resistors/literature/WDBR.pdf>

Overload Conditions



Mounted on a $0.53^{\circ}\text{C}/\text{W}$ heatsink with 5m/s forced air cooling, air temperature 25°C . $\Delta R \leq 5\%$.

Maximum peak current (A)

Value	12R – 25R	47R – 150R
WDBR1UL	21.6	8.1
WDBR2UL	20.5	9.0
WDBR3UL	25.4	11.4
WDBR5UL	27.8	10.2
WDBR7UL	44.5	20.3

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Ordering Procedure

Example: WDBR2UL-100RKLW (WDBR2UL, 100 ohms $\pm 10\%$, with flying leads, Pb-free)



1 Size	2 Certification	3 Solder Type	4 Value	5 Tolerance	6 Terminations	7 Packing		
WDBR1	UL = UL508	Omit for 96SC, standard Pb-free	3/4 characters	K = $\pm 10\%$	I = solder pads	W	WDBR1UL....I	100/box
WDBR2			R = ohms		L = flying leads		WDBR2UL....I	
WDBR3		HT = HMP, high temperature					WDBR1UL...L	40/box
WDBR5							WDBR2UL...L	
WDBR7							WDBR3UL...I	
						WDBR5UL....I	20/box	
						WDBR3UL....L		
						WDBR5UL....L		
						WDBR7UL....I		
						WDBR7UL....L		

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.